

SL™ (Stackable Linear) Modular Connectors

SL™ Key	
• W-to-W (Wire-to-Wire) • W-to-B (Wire-to-Board) • Single Row headers in Vertical and Right Angle • Through hole, SMT, and press fit PCB termination • 22-30 AWG male, female terminals • Terminals with high force contact • IDT (Insulation Displacement Technology) and FFC/FPC (Flat Flex Cable/Flexible Printed Circuitry) wire termination available • Many ways to customize	• Intermates with other Molex families in 2.54mm pitch (see KK® and C-Grid® families on molex.com)
Options Available:	
• "A" versions stackable on X-Y matrix • Positive locking features • TPA (Terminal Position Assurance) eliminates wire backout • Panel mount options available for high vibration environments • 250 max voltage • 3.0A max amperage	

