

C1, D1 & C1, D2 EXPLOSION PROOF FIXTURES

SERIES A, B, C, D, G, H, I & R



A SERIES C1, D2

PART NUMBER: GI-EPA-C250C-C1D2 Compact GI-EPA-C250L-C1D2 Large 60W 8,400 LM 140 LM/W 5000K		PART NUMBER: GI-EPA-C250HO-C1D2 80W 11,200 LM 140 LM/W 5000K	
PART NUMBER: GI-EPA-C400-C1D2 100W 14,000 LM 140 LM/W 5000K		PART NUMBER: GI-EPA-C400HO-C1D2 150W 21,000 LM 140 LM/W 5000K	
PART NUMBER: GI-EPA-C1000EC-C1D2 200W 28,000 LM 140 LM/W 5000K		PART NUMBER: GI-EPA-C1000-C1D2 300W 42,000 LM 140 LM/W 5000K	

For more details,
scan the QR
codes to view
our spec sheets

PART NUMBER:
GI-EPA-C250HO-C1D2

400W
56,000 LM
140 LM/W
5000K



B SERIES C1, D2

PART NUMBER: GI-EPB-C250C-C1D2 Compact GI-EPB-C250L-C1D2 Large 60W 8,400 LM 140 LM/W 5000K		PART NUMBER: GI-EPB-C250HO-C1D2 80W 11,200 LM 140 LM/W 5000K	
PART NUMBER: GI-EPB-C400-C1D2 100W 14,000 LM 140 LM/W 5000K		PART NUMBER: GI-EPB-C400HO-C1D2 150W 21,000 LM 140 LM/W 5000K	

PART NUMBER:
GI-EPB-C1000EC-C1D2

200W
28,000 LM
140 LM/W
5000K



C1, D1 & C1, D2 EXPLOSION PROOF FIXTURES

SERIES A, B, C, D, G, H, I & R




C SERIES

C1, D1


PART NUMBER:
GI-EPC-C175-G4

60W
8,400 LM
140 LM/W
5000K



PART NUMBER:
GI-EPC-C250-G4

80W
11,200 LM
140 LM/W
5000K




PART NUMBER:
GI-EPC-C1000-G4

250W
28,000 LM
140 LM/W
5000K




PART NUMBER:
GI-EPC-C400-G4

100W
14,000 LM
140 LM/W
5000K



PART NUMBER:
GI-EPC-C400HO-G4

150W
21,000 LM
140 LM/W
5000K



D SERIES

C1, D1

PART NUMBER:
GI-EPD-C400-G4

100W
14,000 LM
140 LM/W
5000K



PART NUMBER:
GI-EPD-C400HO-G4
GI-EPD-C400HO-480G4 | 480V

150W
21,000 LM
140 LM/W
5000K



G SERIES

C1, D1

PART NUMBER:
GI-EPG-C150-G4

30W
4,200 LM
140 LM/W
5000K



PART NUMBER:
GI-EPG-C175-G4

40W
5,600 LM
140 LM/W
5000K



H SERIES

C1, D2

PART NUMBER:
GI-EPH-C175C-C1D2 | Compact
GI-EPH-C175L-C1D2 | Large

40W
5,600 LM
140 LM/W
5000K



PART NUMBER:
GI-EPH-C250-C1D2

60W
8,400 LM
140 LM/W
5000K



PART NUMBER:
GI-EPH-C250HO-C1D2

80W
11,200 LM
140 LM/W
5000K



C1, D1 & C1, D2 EXPLOSION PROOF FIXTURES

SERIES A, B, C, D, G, H, I & R



I SERIES C1, D1

PART NUMBER:
GI-EPI-C175-G4

40W
5,600 LM
140 LM/W
5000K



PART NUMBER:
GI-EPI-C250-G4

60W
8,400 LM
140 LM/W
5000K



PART NUMBER:
GI-EPI-C400-G4

80W
12,000 LM
140 LM/W
5000K



PART NUMBER:
GI-EPI-C400HO-G4

100W
14,000 LM
140 LM/W
5000K



R SERIES C1, D2

PART NUMBER:
GI-EPR-C175-C1D2
GI-EPR-C175D-C1D2 | Dimmable

30W
4,200 LM
140 LM/W
5000K



PART NUMBER:
GI-EPR-C250-C1D2
GI-EPR-C250D-C1D2 | Dimmable

50W
6,500 LM
140 LM/W
5000K



SCAN THE QR CODE TO VIEW ON OUR WEBSITE
OR VISIT WWW.GREENIGNITE.COM