


POLYMER

Aluminum Electrolytic Capacitors



ECAS Series

Polymer Aluminum Electrolytic Capacitors




Murata Manufacturing Co., Ltd.'s ECAS series of polymer aluminum electrolytic capacitors are ideal for low ESR, high capacitance applications in a variety of commercial and industrial markets. Utilizing innovative design and manufacturing processes, the ECAS series provides a high level of performance allowing circuit designers to achieve excellent noise suppression, ripple absorption, and output smoothing in power management applications.

Features

- Resin molded case structure utilizes multilayer aluminum foil for anode and solid conductive polymer for cathode
- High capacitance and Low ESR
- High frequency performance up to 500kHz with low impedance for excellent noise suppression
- Stable capacitance with applied voltage
- Stable capacitance with temperature
- Stable capacitance at high operating frequencies
- No voltage derating required
- Polarity bar (positive) noted on product
- Surface mount construction
- RoHS compliant
- Halogen free epoxy
- MSL 3 packaging

Capacitor Map



Polymer Aluminum Electrolytic Capacitors


Appearance



Capacitance Code

Rated Voltage Code
220uF/2V

External Dimensions



Case Size

(Units: mm)

Case Size	EIA Code	L	W	T	W1	S
D4	7343	7.3+/-0.3	4.3+/-0.2	1.9+/-0.1	2.4+/-0.2	1.3+/-0.2
D6	7343	7.3+/-0.3	4.3+/-0.2	2.8+/-0.3	2.4+/-0.2	1.3+/-0.2
D9	7343	7.3+/-0.3	4.3+/-0.3	4.2+/-0.3	2.4+/-0.2	1.3+/-0.2

Specifications

- Capacitance Range: 6.8 to 470μF
- ESR: 6 to 70mΩ
- Rated Voltage: 2 to 16VDC
- Operating Temperature: -40 to 105°C

Product Lineup

Capacitance Value (μF)

	6.8	8.2	10	15	22	33	47	56	68	82	100	150	180	220	270	330	470		
Voltage (VDC)	2	POLYMER & MLCC SOLUTIONS									D4 16	D4 9		D4 9		D4 6	D6 7	D4 4.5	D6 6
	4								D4 20	D4 16		D4 16	D6 12	D6 10		D9 8			
	6.3			D4 55		D4 45	D4 25	D4 25		D4 15		D4 15	D6 10		D9 10				
	10			D4 55		D4 28	D4 25			D6 15		D9 10	D9 10						
	12.5			D4 55	D4 45	D4 30	D6 25	D6 20	D9 20			D9 12			POLYMER SOLUTIONS				
	16	D4 70		D4 60	D4 40	D6 30													

D4 — Case Size
6 — ESR (mΩ)

Mass Production
To Be Released in 2010





POLYMER & MLCC SOLUTIONS

POLYMER SOLUTIONS

Polymer Aluminum Electrolytic Capacitors

Characteristics

Comparison of impedance frequency and capacitance characteristics of 330 μ F/2V



— Murata Polymer Capacitor
(Resin-Molded Chip type)




----- Al (Can type/Polymer)



— Al (Can type/Electrolyte)



Applications




Polymer Aluminum Electrolytic Capacitors


Specification Details

Item	Test Conditions	Characteristics	
Operating Temperature	-	-40 to105°C	
Rated Voltage	-	2 to 16V	
Leakage Current	Applied Voltage: Rated voltage measured after 2 minutes of application	≤ 0.04CV for 2V to 10V products ≤ 0.1CV for 12.5V to 16V products	
Capacitance Value	120Hz @ 25°C	6.8 to 470uF	
Capacitance Tolerance	120Hz @ 25°C	± 20%	
Dissipation Factor	120Hz @ 25°C	≤ 0.06	
ESR	100kHz @ 25°C	6 to 70 mΩ	
Allowable Ripple Current	Measuring Frequency: 100kHz ±10% Measuring Temperature: 20 to 105°C	Ranges from 1 to 3.5Arms; part number specific	
Surge	Test Cycle: 1,000 cycles Applied Voltage: Rated Voltage x 1.25 Test Temp: 85°C for 2V to 10V products Test Temp: 25°C for 12.5V to 16V products	Leakage Current	≤ 0.04CV for 2V to 10V products ≤ 0.1 CV for 12.5V to 16V products
		Capacitance Change	±10% of initial measured value
		Dissipation Factor	≤ 0.06
Endurance	Test Temperature: 105°C ±2°C Applied Voltage: Rated Voltage Test Time: 1,000hrs +48hrs, -0hrs	Leakage Current	≤ 0.04CV for 2V to 10V products ≤ 0.1CV for 12.5V to 16V products
		Capacitance Change	±10% of initial measured value
		Dissipation Factor	≤ 0.06
Moisture Resistance Under Load	Test Temperature: 60°C ±2°C Relative Humidity: 90 to 95% Applied Voltage: Rated Voltage Test Time: 1,000hrs +48hrs, -0hrs	Leakage Current	≤ 0.04CV for 2V to 10V products ≤ 0.1CV for 12.5V to 16V products
		Capacitance Change	-20% and +50% of initial value
		Dissipation Factor	≤ 0.12
Solderability	Solder Temperature: 235°C ±5°C Immersion Time: 5s ±0.5s	Terminal face should be covered 95% by new solder.	

Recommended Pb-Sn Reflow Profile



Land Pattern Design



Polymer Aluminum Electrolytic Capacitors

Part Number Listing

Murata Part Number	Rated Voltage	Cap.	Case Size			Cap Tolerance	ESR Max.	Leakage Current	Ripple Current	Min. Packaging Quantity (Pcs)
	(VDC)	(μ F) 120Hz / 25°C	Code	L x W (mm)	T (mm)	%	(m Ω) 100kHz / +25°C	(CV)	100kHz / +20~105°C	
ECASD40D107M016K00	2	100	D4	7343	1.9	±20%	16	0.04CV	2.0Arms	3,000
ECASD40D157M009K00	2	150	D4	7343	1.9	±20%	9	0.04CV	3.0Arms	3,000
ECASD40D227M009K00	2	220	D4	7343	1.9	±20%	9	0.04CV	3.0Arms	3,000
ECASD60D337M007K00	2	330	D6	7343	2.8	±20%	7	0.04CV	3.5Arms	2,500
ECASD60D477M006K00	2	470	D6	7343	2.8	±20%	6	0.04CV	3.5Arms	2,500
ECASD40G686M020K00	4	68	D4	7343	1.9	±20%	20	0.04CV	1.9Arms	3,000
ECASD40G826M016K00	4	82	D4	7343	1.9	±20%	16	0.04CV	2.1Arms	3,000
ECASD40G157M016K00	4	150	D4	7343	1.9	±20%	16	0.04CV	2.1Arms	3,000
ECASD60G187M012K00	4	180	D6	7343	2.8	±20%	12	0.04CV	2.5Arms	2,500
ECASD60G227M010K00	4	220	D6	7343	2.8	±20%	10	0.04CV	3.0Arms	2,500
ECASD90G337M008K00	4	330	D9	7343	4.2	±20%	8	0.04CV	3.3Arms	2,000
ECASD40J106M055K00	6.3	10	D4	7343	1.9	±20%	55	0.04CV	1.0Arms	3,000
ECASD40J226M045K00	6.3	22	D4	7343	1.9	±20%	45	0.04CV	1.0Arms	3,000
ECASD40J336M025K00	6.3	33	D4	7343	1.9	±20%	25	0.04CV	1.8Arms	3,000
ECASD40J476M025K00	6.3	47	D4	7343	1.9	±20%	25	0.04CV	1.8Arms	3,000
ECASD40J686M015K00	6.3	68	D4	7343	1.9	±20%	15	0.04CV	2.0Arms	3,000
ECASD40J107M015K00	6.3	100	D4	7343	1.9	±20%	15	0.04CV	2.0Arms	3,000
ECASD60J157M010K00	6.3	150	D6	7343	2.8	±20%	10	0.04CV	3.0Arms	2,500
ECASD90J227M010K00	6.3	220	D9	7343	4.2	±20%	10	0.04CV	3.0Arms	2,000
ECASD41A106M055K00	10	10	D4	7343	1.9	±20%	55	0.04CV	1.0Arms	3,000
ECASD41A226M028K00	10	22	D4	7343	1.9	±20%	28	0.04CV	1.6Arms	3,000
ECASD41A336M025K00	10	33	D4	7343	1.9	±20%	25	0.04CV	1.8Arms	3,000
ECASD61A686M015K00	10	68	D6	7343	2.8	±20%	15	0.04CV	2.0Arms	2,500
ECASD91A107M010K00	10	100	D9	7343	4.2	±20%	10	0.04CV	3.0Arms	2,000
ECASD91A157M010K00	10	150	D9	7343	4.2	±20%	10	0.04CV	3.0Arms	2,000
ECASD41B106M055K00	12.5	10	D4	7343	1.9	±20%	55	0.1CV	1.0Arms	3,000
ECASD41B156M045K00	12.5	15	D4	7343	1.9	±20%	45	0.1CV	1.0Arms	3,000
ECASD41B226M030K00	12.5	22	D4	7343	1.9	±20%	30	0.1CV	1.6Arms	3,000
ECASD61B336M025K00	12.5	33	D6	7343	2.8	±20%	25	0.1CV	1.8Arms	2,500
ECASD61B476M020K00	12.5	47	D6	7343	2.8	±20%	20	0.1CV	2.0Arms	2,500
ECASD91B566M020K00	12.5	56	D9	7343	4.2	±20%	20	0.1CV	2.0Arms	2,000
ECASD91B107M012K00	12.5	100	D9	7343	4.2	±20%	12	0.1CV	2.5Arms	2,000
ECASD41C685M070K00	16	6.8	D4	7343	1.9	±20%	70	0.1CV	1.0Arms	3,000
ECASD41C106M060K00	16	10	D4	7343	1.9	±20%	60	0.1CV	1.0Arms	3,000
ECASD41C156M040K00	16	15	D4	7343	1.9	±20%	40	0.1CV	1.0Arms	3,000
ECASD61C226M030K00	16	22	D6	7343	2.8	±20%	30	0.1CV	1.6Arms	2,500

MSL 3 Packaging (moisture sensitivity level)

Polymer Aluminum Electrolytic Capacitors

Part Number Breakdown

Part Numbering

ECAS	D4	0D	227	M	009	K	00
1	2	3	4	5	6	7	8

1 Series

Code	Product
ECAS	Chip Type Polymer Al Capacitor

2 Case Size (LxWxT) (mm)

Code	L	W	T
D4	7.3+/-0.3	4.3+/-0.2	1.9+/-0.1
D6	7.3+/-0.3	4.3+/-0.2	2.8+/-0.3
D9	7.3+/-0.3	4.3+/-0.3	4.2+/-0.3

3 Rated Voltage

Code	Rated Voltage
0D	DC 2V
0E	DC 2.5V
0G	DC 4V
0J	DC 6.3V
0K	DC 8V
1A	DC 10V
1B	DC 12.5V
1C	DC 16V

4 Capacitance

Code	Capacitance
476	47uF
107	100uF
227	220uF
477	470uF

5 Capacitance Tolerance

Code	Tolerance
M	+/-20%

6 ESR

Code	ESR
4R5	4.5mΩ
009	9mΩ
010	10mΩ

7 Packaging

Code	Packaging
K	Φ330mm Plastic Taping

8 Individual Specification Code

Series Cross Reference

Manufacturer	P/N Prefix / Series	Brand	MuRata	Series Name
Panasonic	EEF	SP-Cap	MuRata	ECAS
Kemet	A700	AO-CAP	MuRata	ECAS
Showa Denko	A705	SDK-CAP	MuRata	ECAS
Rubycon	SXB, SXE, SW	PC-CON	MuRata	ECAS
NIC	NSP, NPC	—	MuRata	ECAS
Cornell Dublier	ESR, SPA, SPSX, SPCX	—	MuRata	ECAS

For a detailed competitor cross reference please visit: www.murata-northamerica.com/polymer_al

Innovator in Electronics

△ Note:

1. Export Control

<For customers outside Japan> Murata products should not be used or sold for use in the development, production, stockpiling or utilization of any conventional weapons or mass-destructive weapons (nuclear weapons, chemical or biological weapons, or missiles), or any other weapons.

<For customers in Japan> For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- | | |
|-----------------------------|---|
| ① Aircraft equipment | ② Aerospace equipment |
| ③ Undersea equipment | ④ Power plant equipment |
| ⑤ Medical equipment | ⑥ Transportation equipment (vehicles, trains, ships, etc.) |
| ⑦ Traffic signal equipment | ⑧ Disaster prevention / crime prevention equipment |
| ⑨ Data-processing equipment | ⑩ Application of similar complexity and/or reliability requirements to the applications listed above. |

3. Product specifications are subject to change or our products may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

4. Please read rating and △ CAUTION (for storage, operating, rating, soldering, mounting and handling) to prevent smoking and/or burning, etc.

5. Please approve our product specifications or complete the approval sheet for product specifications before ordering.

6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

8. For status of RoHS compliance of our products, please consult our website.



Murata Manufacturing Co., Ltd.

Head Office

1-10-1, Higashi Kotari 1-chome
Nagaokakyo-shi, Kyoto
617-8555, Japan
Phone: 81-75-951-9111

International Division

3-29-12, Shibuya 3-chome,
Shibuya-ku, To kyo
150-0002 Japan
Phone: 81-3-5469-6123

Murata Electronics North America, Inc.

2200 Lake Park Drive
Smyrna, GA 30080-7604, USA.
Phone: 1-770-436-1300
Fax: 1-770-436-3030

For additional Polymer information visit:

www.murata-northamerica.com/polymer_al

Murata (China) Investment Co., Ltd.

Lane 318 Yonghe Road
Zhabei District, Shanghai 200072, China
Phone: 86-21-3205-4616
Fax: 86-21-3205-4617

Murata Electronics (Netherlands) B.V.

Daalmeersstraat 4, 2131HC Hoofddorp
The Netherlands
Phone: 31-23-5698360
Fax: 31-23-5698361

Taiwan Murata Electronics Co., Ltd.

No 225 Chung - Chin Road, Taichung, Taiwan
Phone: 886-4-2425-4151



Innovator in Electronics

Cat. No. C-40-A

4-2010

©2010 Murata Electronics North America, Inc.