



A Leading Magnetics Supplier to Serve Global Markets

CODADA offers high efficiency and high reliable magnetics components solutions to serve global customer

Products Highlights

- Lightweight design
- Saturation current up to 300A
- Increased power density and power conversion
- Advanced materials and construction for highly efficiency and ultra-low DC resistance
- No thermal aging
- Low EMI noise

Codaca's Strength

- FeSi/ FeSiAl/FeNi core manufacturing
- Advanced metal alloy powder cores
- Molded construction techniques
- Litz wire / Flat Windings
- Automation equipment team
- Customize available
- Online design tools
- IC reference design

Quality Management

Total Quality Control (TQC) Principles

- Not accept defective products
- Not manufacture defective products
- Not transfer defective products
- Zero defect, APQP

Management Certification

- ISO9001
- ISO14001
- IATF16949
- CNAS for lab

Resource Guarantee

- Measurement lab
- Analytical lab
- Environmental lab

Design Tool

Support Quick Power Inductor Selection

Cross Reference Inductor Finder

Power Inductor Loss Comparison

Reference Design Inductor Finder

DCR Temperature Calculator

