



Life Energy Motion

HIGH PRECISION SOLUTIONS


Electrical Measurement Solutions for High Precision Applications



High Precision Solutions

Highly precise current measurement is key to equipment performance. Minor inaccuracies can lead to major problems. High precision current sensors accurately measure electrical current, typically in applications where precision is critical, such as in industrial automation, renewable energy, power supplies, and high-end electronics. These sensors are designed to deliver highly accurate readings even in the presence of noise or varying environmental conditions. Whether for medical equipment or other industrial applications, LEM's current sensors set the standard for precise current measurement and accuracy.

Electrical Layout:



CV



DV



IN



IST




IT

Bandwidth	6kHz - 700kHz	12kHz	140kHz - 1100kHz	60Hz	500kHz - 800kHz
Consumption	32mA - 35mA	25mA	0.07A - 1.87A	200W	80mA
Current Range Max	130V - 6000V	1200V - 4200V	300A - 3000A	60A - 2000 A	60A - 1000A
Supply Voltage	15V - 24V	13.5V - 26.4V	15V	100V - 240 V	15V
Mounting	Panel	Panel	Panel	-	Panel
Output	Voltage	Voltage	Current	Voltage / Current	Current
Overall Accuracy	0.2% - 1%	0.3% - 1.2%	0.0012% - .0075%	-	0.02725%
Technology	Closed Loop Fluxgate	Insulation Digital	Closed Loop Fluxgate	Power Supply	Closed Loop Fluxgate


Medical Equipment

Medical devices, such as imaging equipment, surgical instruments, ventilators, and diagnostic systems, must operate within strict current limits to avoid damaging sensitive components, ensure patient safety, and maintain regulatory compliance. MRI machines utilize high-power magnets to create detailed images. Accurate current sensors are required to control the power supplied to these magnets, ensuring image quality and patient safety. Any fluctuations in the current can cause distortions in the magnetic field, affecting image clarity.



Equipment Validation

Equipment validation ensures industrial equipment meets the required standards of accuracy, reliability, and performance for its intended use. This is critical in industries such as manufacturing, aerospace, medical devices, pharmaceuticals, and energy, where equipment must operate within tight tolerances to produce consistent, high-quality outputs. High precision current sensors are essential during this process ensuring machinery operates within design specifications, detecting potential issues such as overcurrent, short circuits, or inefficient power consumption.



ITC 2000



ITC 4000



ITL




ITN



ITZ

27kHz	82kHz	50kHz	100kHz - 500kHz	2kHz - 300kHz
70mA	70mA	0.35A	60mA - 130mA	76W - 300W
3000A	6000A	12000A	12.5A - 1000A	2000A - 24000A
24V	24V	24V	15V	100V - 240V
Panel	Panel	Panel	PCB, Panel	Panel
Current	Current	Current	Current	Current
0.05%	0.05%	0.06%	0.00115% - 0.0509%	0.0004% - 0.0008%
Closed Loop Fluxgate	Closed Loop Fluxgate	Closed Loop Fluxgate	Closed Loop Fluxgate	Closed Loop Fluxgate

Global Support Network



Locations:

Americas:

LEM USA, Inc.
11665 W Bradley Road
Milwaukee, WI 53224
Tel. +1 800 236 5366

Bulgaria:

LEM Bulgaria EOOD
ul. "Iliyansko Shose" 8
1220 Sofia, Bulgaria
Tel. +359 2 424 6333

China:

LEM Electronics (China) Co., Ltd.
Linhe Street 28, Shunyi District
CN-101300 Beijing
Tel. +86 10 8945 5288

Europe:

LEM Europe GmbH
Frankfurter Street 74
64521 Groß-Gerau, Germany
Tel. +49 6152 93010

Headquarters:

LEM International SA
Route du Nant-d'Avril 152
1217 Meyrin, Switzerland
Tel. +41 22 706 11 11

Japan:

LEM Japan KK
2-1-2 Nakamachi
Machida, Tokyo 194-0021, Japan
Tel. +81 42 725 8151

Malaysia:

LEM Malaysia DN BHD
Jalan PSPN 3
14100 Simpang Ampat, Pulau Pinang, Malaysia

South Korea:

LEM Management Services Sàrl
FASTFIVE #311, #312
10 Nambusunhwan-ro 333-gil
Seocho-gu, Seoul 06725, Korea
Tel. +82 10 7150 2450

LEM

Life Energy Motion

